


840 series hygienic pump

800 series Watson-Marlow Pumps

FEATURES


- Flow rates from 653 L/h to 8,140 L/h (1.33 L/rev)
- Clean-in-place and steam-in-place sterilisation at full velocity with no bypass required
- Bioprene tube to USP Class VI and hygienic stainless steel connectors certificated to 3.1.B BS/EN 10204.
- Bioprene tubing available in two hardnesses for pressures up to 2 bar and 3.5 bar.
- Pumpheads to accept B5 output flange-mounted gear motors in a range of single and three phase fixed and electronic variable speeds
- Hinged door with only two captive bolts makes tube inspection and change extremely simple and safe



Watson-Marlow...Innovation in Full Flow


PERFORMANCE

Speed (rpm)	Flow rate (L/hr)	Fitted motor power (kW)	Speed (rpm)	Flow rate (L/hr)	Fitted motor power (kW)
8	653	0.55	42	3352	1.1
10	790	0.55	47	3751	1.5
13	1045	0.55	52	4150	1.5
16	1277	0.55	58	4628	1.5
22	1756	0.75	65	5187	1.5
25	1995	0.75	73	5825	2.2
29	2314	1.1	79	6304	2.2
33	2649	1.1	89	7102	2.2
36	2905	1.1	102	8140	3



For variable speed units and other build options, please contact your local representative, or the Watson-Marlow Applications Engineering department.

TECHNICAL DRAWINGS



TECHNICAL SPECIFICATIONS

Environment temperature	5C to 40C (40F to 104F)
Fluid temperature	0C to 80C (-32F to 175F)
Max pressure	3.5 bar
Pump weight	Dependant upon drive. Nominally 130kgs
Noise	<75dB(A) at 1m

MATERIALS OF CONSTRUCTION

Component	Material
Pumphead body	Aluminum alloy with epoxy polyester powder coat finish
Pumphead door	Aluminum alloy with epoxy polyester powder coat finish
Pumphead rotor hub	Aluminum alloy with epoxy polyester powder coat finish
Rotor rollers	Stainless steel 316
Support frame	Stainless steel 304
Door fixings	Stainless steel
Motor fixings	Zinc plated high tensile steel bolts, stainless steel nuts and washers
Frame fixings	Stainless steel

All flow rates shown were obtained pumping water at 20C (68F) with zero suction and delivery heads. Watson-Marlow, Bioprene and Marprene are trademarks of Watson-Marlow Limited. Disclaimer: The information contained in this document is believed to be correct but Watson-Marlow Limited accepts no liability for any errors it contains, and reserves the right to alter specifications without notice. LoadSure is a trademark of Watson-Marlow Limited. © STA-PURE PFL and © STA-PURE PCS are registered trademarks of W.L Gore & Associates Inc. Please state the product code when ordering pumps and tubing.

**WATSON
MARLOW
Pumps**

wmftg.com
info@wmftg.com
+44 (0) 1326 370370